

# fend-all® Porta Stream® II + III

Porta Stream II and III offer versatile portability and 15-minutes of uninterrupted flushing — without costly plumbing. Porta Stream's simplicity of installation and operation has made it a popular choice. Self-contained, each model features a nozzle strap that is easily removed to activate flushing, leaving hands free to hold eyelids open. Porta Stream III (inset photo) is freeze protected by a special form fitted insulated cover and twin, 600 watt, 110 volt thermostatically controlled heaters for indoor and outdoor use. The fluid-heating system makes it ideal for use between 72° and -32° F (22° to -36° C). Each portable unit may be mounted on a wall, mobile cart or mobile stand.

**15-Minute  
Flush Time**  
Economically Meets  
ANSI Standard



**PRIMARY DEVICE**

## FEATURES:

- **Self-contained/no plumbing**
- **Fluid flushing options**
- **Green color**
- **15-minute flow cycle**
- **Efficient "full-flow" nozzles**
- **Easy-to-use nozzle strap**
- **Sturdy, molded construction**
- **Large fill hole/lockable fill cap**
- **Illustrated operating instructions**

## BENEFITS:

Easy installation with no plumbing required. Can be easily and affordably placed near most workplace hazards with single bracket mounting device or transported with optional universal cart or universal stand. Molded handle accepts hanging bracket for vertical or horizontal surface installation.

Versatile flushing fluid options include Eyesaline® — a preserved, buffered, saline solution superior to tap water for emergency eye care, and Fend-all Water Additive.

Highly visible green color provides easy identification in an emergency situation.

Large 16 gallon (60.5L) capacity permits thorough flushing by providing 0.4 gpm over the entire 15-minute flushing period required by ANSI Z358.1-2004.

Nozzles cover a wide area around the eyes.

Simple strap design is easily removed for hands-free flushing, leaving hands free to hold eyelids open.

Properly installed, the system may be safely leaned upon during use.

Simplifies refilling and cleaning, and reduces risk of possible tampering.

Easy-to-use design features simple, highly visible operating instructions on the unit itself.

	MODEL NO.	MEETS ANSI Z358.1-2004	TIME CYCLE/ FLOW RATE	INCLUDES FEND-ALL SOLUTION	MAINTENANCE	SHIPPING DIMENSIONS/WEIGHT			
<b>Porta Stream II</b>	32-000200-0000† (English)	YES* (Primary Device)	15 minutes/0.4 gpm	Eyesaline Concentrate	6 month change/cleaning	26" x 20" x 20"/35lbs.			
	32-000200-0022 (French Canadian)	YES* (Primary Device)	15 minutes/0.4 gpm	Eyesaline Concentrate	6 month change/cleaning	26" x 20" x 20"/35lbs.			
	32-000200-0070 (Mexican Spanish)	YES* (Primary Device)	15 minutes/0.4 gpm	Eyesaline Concentrate	6 month change/cleaning	26" x 20" x 20"/35lbs.			
	32-000230-0000 (English)	YES* (Primary Device)	15 minutes/0.4 gpm	Fend-all Additive	4 month change/cleaning	26" x 20" x 20"/23lbs.			
	32-000230-0022 (French Canadian)	YES* (Primary Device)	15 minutes/0.4 gpm	Fend-all Additive	4 month change/cleaning	26" x 20" x 20"/23lbs.			
	32-000230-0070 (Mexican Spanish)	YES* (Primary Device)	15 minutes/0.4 gpm	Fend-all Additive	4 month change/cleaning	26" x 20" x 20"/23lbs.			
<b>Porta Stream III</b>	32-000310-0000† (freeze protected)	YES* (Primary Device)	15 minutes/0.4 gpm	Eyesaline Concentrate	6 month change/cleaning	26" x 20" x 20"/44lbs.			
<b>RECOMMENDED REFILLS &amp; ACCESSORIES</b>			See Pages 90 and 91 for more information.						
Eyesaline Solution	Eyesaline Concentrate	Fend-all Water Additive	Universal Cart	Universal Stand	Reflective Cover	Dust Cover	Fluid Disposable Cart	Waste Container	Cleaning Kit
32-000502-0000	32-000513-0000	32-001100-0000	32-001060-0000	32-001065-0000	32-000532-0000	32-000517-0000	32-001060-0000	32-001061-0000	32-000518-0000



†Models include emergency eyewash sign.

\*Meets the ANSI Z358.1-2004 Standard for continuous 15-minute flushing requirement.